



RMQ-Titan pilot devices: Chemical resistance

Over 100 years of experience

The products in the RMQ-Titan range are made of a variety of different materials and components. With over 100 years of experience in developing and producing pilot devices of the Eaton Moeller series, we know exactly which materials to use, and how and where they should be used.

Before new products are brought to market, they are thoroughly tested to ensure they meet the high quality standards of our company and our customers. The tests are carried out by the Institute for International Product Safety (I²PS), which is an independent testing laboratory.

Resistance

The resistance of materials to different materials and chemicals is highly dependent on various factors, such as

- Duration and frequency of exposure
- Concentration of the medium
- Temperature

The listed data is based on laboratory tests and past experience, serving as a guideline for the materials used in our pilot devices. If the products are to be used in a particular environment, they may need to be tested under real-life conditions in specific cases.



EATON

Powering Business Worldwide

All data is based on tests conducted at room temperature and, unless stated otherwise, using the standard concentration of media.

Resistant	Partially resistant	Non-resistant
• Acidic disinfectant • Alkaline cleaning agent (chlorine-free) • Acidic foam cleaning agent • Neutral disinfectant • Diluted mineral acids • Diluted alkaline solutions • Tap water • Car cleaning solution • Water-based cooling lubricants • Animal oils • Oleic acid • Octanoic acid	• Alkaline cleaning agent (containing chlorine) • Mineral oil • Diesel fuel • Fuel oil • Kerosene / Paraffin • White spirit • Lactic acid • Alcohols	• Regular gasoline • Concentrated mineral acids • Concentrated alkaline solutions

The following tests were performed using commercially available disinfectants and cleaning agents:

Media	Application	Concentration	pH value	Ingredients	Resistance
P3-topactive DES	Acidic disinfectant	3%	3	Hydrogen peroxide 8–35% Acetic acid <10% Alkyl amine oxides 1–5% Peracetic acid 1–5%	++
P3-topactive 200	Alkaline cleaning agent (chlorine-free)	4%	13	Ethanol 5–10% Sodium hydroxide 5–10% Potassium hydroxide 7–25% Anionic surfactants 1–5% Alkyl polyglycosides 1–5% Alkyl amine oxides <1%	++
P3-topax 65	Alkaline cleaning agent (containing chlorine)	5%	13.5	Potassium hydroxide 5–7% Sodium hypochlorite 2.5–5% Alkyl amine oxides 1–5%	+
BCS aluminum cleaner	Acidic foam cleaning agent	2%	1.5	Phosphoric acid 25–50% Nitric acid 10–25% Polyethylene glycol monododecyl ether <2.5% Amines, C10-16-alkyldimethyl, N-oxides <2.5%	++
Fink Antisept G	Neutral disinfectant	5%	8.	Alkyldimethylbenzylammonium chloride 5–10% Didecyldimethylammonium chloride 2.5–5%	++

Resistance: ++ = resistant; + = partially resistant; - = non-resistant

Testing conditions:

Temperature = room temperature

Type of exposure = dipped

Duration of exposure = 28 days

Concentration = (manufacturer's recommended concentration)

If you have any further questions, please contact your distributor or visit [Eaton.com/contacts](https://www.eaton.com/contacts)

The products, information and prices contained in this document are subject to change. We also reserve the right to correct any errors or omissions. Only order confirmations and technical documentation received from Eaton are binding. Images and illustrations are indicative only and do not guarantee any particular design or functionality. Their use in any form must be approved in advance by Eaton. The same applies to trademarks (especially to Eaton, Moeller, Cutler-Hammer, Cooper and Bussmann). Eaton's terms of sale apply, as published on Eaton's web pages and included with order confirmations received from Eaton.

Eaton Industries GmbH
Hein-Moeller-Str. 7–11
D-53115 Bonn, Germany
[Eaton.com](https://www.eaton.com)

© 2022 Eaton
All Rights Reserved
Publication No. FL047011EN
March 2022

Eaton is a registered trademark.

All other trademarks are the property of their respective owners.



Powering Business Worldwide